

# PX774D-1

A high performance, rubber modified epoxy adhesive

## **Application**

Bonding of dissimilar materials

## **Key Properties**

- Excellent adhesion to a variety of metals
- Non-toxic
- Thixotropic
- High impact resistance
- Excellent rubber and plastic adhesive

## Description

Basic Two-component epoxy system

ResinRX774D-1HardenerHX774D-1

Physical Data (approx. – values)			
	Resin	Hardener	Mixed
Colour	Black	Amber	Black
Specific Gravity	1.2	0.96	1.01
Viscosity (mPas) @ 25°C	Thixotropic	Thixotropic	Thixotropic

Cure Schedule (150ml sample)				
Temperature	Working Life (minutes)	Gel Time (minutes)	Light Handling (hours)	Full Cure (hours)
10°C	25	90	16	32
20°C	20	60	8	16
30°C	10	30	4	8

<sup>\*</sup>RT is defined as 20-25°C

Cure time will depend on cross sectional area, ambient conditions and mixing method.

The above are typical values and will vary depending on the cured mass and application. Hotter temperatures may be used for faster cure but will result in higher post cure shrinkage and higher cure exotherm. Experimentation and testing is suggested to avoid side effects. For maximum properties a post cure may be required – Contact our technical service department for advice.

## Processing

Mix ratio by weight 0.6:1 Mix ratio by volume 1:2

Approvals		
RoHS compliant	Yes	
UL94 V-0	No	
REACH (SVHC concentration)	0%	

Typical Properties			
Test	Result	Unit	
Hardness	90	Shore A	
Operating Temperature	-65 to +140	°C (Application and geometry dependant)	
Thermal Conductivity	0.25	W/mK	
Tensile Strength	18	MPa	
Compressive Yield Strength	< 10	MPa	
Coefficient of Linear Expansion	80-100	ppm/C	
Volume Resistivity	1.3 x 10 <sup>12</sup>	ohmm.cm	
Electric Strength	22	kV/mm	
Water Absorption (7 days @ 23°C)	0.35	%	

Lap Shear			
Aluminium to Aluminium	17.8 MPa	ABS to ABS	3.1 MPa
Copper to Copper	14.7 MPa	Nylon 6 to Nylon 6	4.3 MPa
Stainless Steel	17.3 MPa	Acrylic to Acrylic	2.6 MPa

<sup>\*</sup> Will depend on cross section area and ambient temperature

#### Packaging

Available in Bulk, Twinpacks, Kits & Cartridges

#### **Availability**

Available through distribution www.resins-online.com and sales@robnor.co.uk

# Cartridge Mixing Part Numbers

PX774D-1/BK/050TC PX774D-1/BK/200TC

It is essential for best results that the cartridge is 'balanced' before use to ensure correct mixing.

Loading the cartridge into the gun before attaching the mixer element and pumping the gun to push a small amount of the contents forward will achieve this. Wipe the excess from the cartridge tip and add the static mixer. The cartridge is now ready for use.

#### **Twinpacks Part Numbers**

Available on request

Twinpacks are pre-weighed resin and hardener components contained in a tough flexible film, separated by a removable clip and rail. Once the clip and rail is removed the resin and hardener is thoroughly mixed within the bag and is immediately ready for use. Mixing will normally take ~ 2 minutes due to the viscosity; but pay special attention to the corners. Twinpacks are ideal for small to medium production runs, prototyping and on-site or field use. The twinpack weight/volume may also be tailored to a specific size on request.

For further details please visit <u>www.robnor-resinlab.com</u>

# Bulk Materials Part Numbers

RX774D-1/BK/10KG HX774D-1/NC/10KG

Both resin and hardener are supplied in 5kg, 25kg and 200ltr drums and fully evacuated and ready for use.

Care should be taken to ensure when mixing the resins air is not entrained in the mixture. If this is unavoidable the mixed resin and hardener should be re-evacuated before dispensing. The bulk resin and hardener materials can be dispensed from suitable dispensing machinery, details provided by Fluid Research on request.

## Kits & Sets Part Numbers

Available on request

Kits and Sets are provided in separate containers to the correct ratio.

In Kit form, pour the hardener into the larger resin container and use it as a mixing vessel.

Stir well using an appropriate mixer until homogeneous.

Note: Incomplete mixing will be characterised by erratic or partially incomplete cure even after extended time periods.

## Cleaning

All equipment contaminated with mixed material should be cleaned before the material has hardened. TS130 is a suitable non-flammable cleaning agent, although other solvents may be found suitable. TS130 will also remove cured material provided it is allowed to soak for a number of hours.

## Storage and Shelf Life

Material stored in the original unopened containers under cool dry condition between 15° and 25°C will have a shelf life of at least two years.

Once used the containers must be kept sealed to prevent effects from water, air or contaminants.

## Health and Safety

Epoxy resin systems may cause sensitisation by skin contact or inhalation may be corrosive, harmful or toxic. It is therefore strongly recommended that skin and eye contact is avoided by the using of appropriate personal protective equipment such as gloves, safety glasses or goggles and overalls. Wash any contamination from the skin immediately and thoroughly and do not eat, smoke or drink in the working vicinity.

Under normal working conditions a good source of ventilation is adequate, however if the material is heated, or where vapour levels are likely to exceed the occupational exposure limits appropriate respiratory protection must be worn. Local exhaust ventilation (LEV) may be required especially for curing ovens or where large volumes of material are curing. The above is given as a guide only; please refer to RX/HX774D-1 Health and Safety data or our Technical Service Department for individual/specific

# Copyright & Warranty - Robnor Resinlab Limited

The results and information above does not constitute a specification and is given in good faith and without warranty. The information is derived from test/or extrapolations believed to be reliable and is quoted for guidance only. The product is offered for evaluation on the understanding the customer satisfies himself that the product is suitable for the intended application by proper evaluation and testing.

# **Contact Details**

Robnor Resinlab Limited Tel: +44 (0) 1793 823741 31 Athena Avenue Fax: +44 (0) 1793 827033

Elgin Industrial Estate

SwindonEmail:support@robnor.co.ukSN2 8EJWeb:www.robnor-resinlab.com

United Kingdom Buy Online: <u>www.resins-online.com</u> (UK only)